

PRODUCT INFORMATION SUMMARY

C126 : RA2

advanced rinse aid for all water hardness for standard enclosed glass and dishwa

Description of product

Suitable for all water conditions Ensures sparkling crockery and cutlery Spot free glassware Low foaming formulation

Product Uses

RA2 is a concentrated machine dishwashing rinse aid for enclosed cabinet dishwashers. It ensures streak free rapid drying in all water conditions. Suitable for use in all dishwashing machines.


Directions

Normally a concentration of 0.1-0.3 ml/l is used, dependent on level of water hardness. The temperature of the wash cycle should be at between 80 - 90°C. PROTECT FROM FROST



iN Insight Supported

iN Insight is Selden's interactive product selection and training system. Enables the user to create full COSHH training kits, wallcharts, task cards and more. visit <http://www.selden.co.uk/insight>



iN Insight recommended product uses

Catering - dish washing rinse aid

Catering - glasswash rinse aid

typical dilution

auto dose

see label

Product Hazards and PPE Requirements

Warning



Contains :

Risk Phrases

Causes serious eye irritation.

Safety Phrases

Keep out of reach of children. Wash hands thoroughly after handling. Wear eye protection. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical attention.

Technical Data

Composition	A blend of low foaming free rinsing detergents
Appearance	Clear liquid
Colour	Blue
Density	1.025
pH	1.7 - 2.5
Fragrance	Odourless
Stability	2 Years in unopened containers at ambient temperatures.

Environmental Profile

Biodegradability

All surfactants contained in Selden Products meet the requirements of the EU Detergent Directive 2005 – 2004/648/EC. This requires all surfactants to break down both quickly and completely into harmless material such as CO2 and water.

Selden Environmental Charter

- We set ourselves industry leading standards.
 - Selden minimises wastage, packaging and transportation.
 - If it can be recycled, it will be recycled.
 - Our chemicals policy exceeds regulatory requirements.
 - We don't expect other people to clean up after us.
 - Conserving energy, preserving resources.
 - By being innovative, we strive to do better.
 - We like to work in partnership with our clients.
- Visit our website for more information.

External Accreditations

9001 - Quality System
14001 - Environmental System
18001 - Health & Safety System
IPPC Certified Manufacturer

Sustainability

Product conforms with the DEFRA endorsed Sustainable Cleaning guidance



COSHH+ Supported

Selden's bespoke COSHH awareness and product training tool. Users specify the products in use and instantly generate a full training pack to enable quick and effective staff training.



www.flagship-mcp.com

Flagship products are those products that are included in Selden Multi-language Cleaning Programme. Flagship products have induction kits, best practise guidance, MSDS, wallcharts and usage guides available in the following languages



english, french, spanish, portuguese, polish, german, dutch, russian, romanian, estonian, czech, croatian.



UKAS
accredited testing
laboratory No. 4204



SELDEN
formulating
testing
manufacturing
to
the highest
standards

Selden Research Limited

Staden Business Park, Staden Lane, Buxton
Derbyshire. SK17 9RZ

Tel : 01298 26226 | Fax : 01298 26540 | Email : info@selden.co.uk | web : www.selden.co.uk

